

TECHSPEC[®] C-Mount, 35mm Sq. x 1mm Thick Plate Mount



Stock **#56-264** 3 In Stock

-

1

+

€292^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€292,00 each
Qty 5-9	€257,70 each
Qty 10-25	€237,20 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Function:

Optic Mount (Fixed)

Type of Optics:

Square

Note: Includes one C-Mount Aperture Cap (#55-245)	
Dimensions of Compatible Optics (mm): 35.0 Sq.	
Physical & Mechanical Properties	
Dimensions (mm): 38.0 x 38.0 x 50.0	
Extension Length (mm): 38.0	
Min. Thickness of Compatible Optics (mm): 1.0	
Max. Thickness of Compatible Optics (mm): 1.0	
Threading & Mounting	
Thread Type: C-Mount	
Compatible Post: 1/4-20	
Regulatory Compliance	
Certificate of Conformance: View	

PRODUCT DETAILS

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
 - Provides a 90° Mounting Interface
 - 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems
- TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.
- Note:** [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

TECHNICAL INFORMATION

