

[See all 17 Products in Family](#)

Mounted M22.5 x 0.5 - UV Cut-Off Filter



Mounted UV Filters

Stock **#58-647** **3 In Stock**

-

1

+

€104⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€104,00 each
Qty 10+	€99,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Mounted Imaging Filter	Type:
Physical & Mechanical Properties	
18.5	Clear Aperture CA (mm):
24.0	Outer Diameter (mm):

5.00	Thickness with Mount (mm):
2.00 ±0.2	Thickness (mm):

2.5	Substrate Thickness (mm):
-----	---------------------------

Optical Properties

390.00	Cut-On Wavelength (nm):
L-39	Glass/Filter Number:

Hoya L-39	Substrate: ☐
Uncoated	Coating:

Clear	Color:
80-50	Surface Quality:

350 - 2200	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):

Threading & Mounting

M22.5 x0.50	Filter Thread:
5.2 ±0.3	Mount Thickness (mm):

7	Mount Thickness Including Threads (mm):
---	---

Environmental & Durability Factors

-15 to +70	Operating Temperature (°C):
------------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	Reach 242:
-----------	------------

Product Details

- Blocks UV and Transmits Visible
- Ideal as Dust or Protective Covers for Camera Sensors

Mounted UV Filters are offered with standard photographic and lens filter mount threads. These filters are ideal for applications where UV light needs to be blocked and visible light passed. The mounted clear aperture is 5mm less than the mount diameter. The maximum outer diameter is 2mm greater than the mount diameter, except for the 62mm and 72mm, which are 3mm larger. Mounted UV Filters are clear in color and non-rotatable.

Technical Information



