

Mounted M30.5 x 0.5 Threaded - Red Filter



Stock #46-545 In Stock

⊖ 1 ⊕ **€53,50**

ADD TO CART

Qty 1-9

€53,50

Qty 10+

€49,40

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
27.0

Filter Thread:
M30.5 x 0.50

Color:
Red

Cut-On Wavelength (nm):
600.00

Glass/Filter Number:
R-60

Index of Refraction n_d :
1.53

Note:
AR Coating: MgF₂

Outer Diameter (mm):
32.0

Substrate:
Colored Glass

Substrate Thickness (mm):
2.0

Surface Quality:
80-50

Thickness of Compatible Optics (mm):
2.0

Thickness with Mount (mm):
5.00

Type:
Mounted Imaging Filter

Type of Filter:
Hoya R-60 or equivalent

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS:
[Exempt](#)

Certificate of Conformance:
[View](#)
