

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

Mounted M72 X 0.75 - UV Cut-On Filter



Mounted UV Filters

Stock #54-048 □ In Stock



1



€58,00

ADD TO CART

Qty 1-9

€58,00

Qty 10+

€53,70

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
67.0

Cut-On Wavelength (nm):
390.00

Filter Thread:
M72 x0.75

Glass/Filter Number: L-39
Substrate: □ Hoya L-39
Operating Temperature (°C): -15 to +70
Coating: AR Coated
Color: Clear
Outer Diameter (mm): 75.0
Thickness with Mount (mm): 5.50
Surface Quality: 80-50
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Type: Mounted Imaging Filter
Coating Specification: R _{avg} >2% @ 400 - 700nm
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 4 - 6λ

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View