

SCHOTT N-WG-295, 25.4mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#46-417** 3-4 DAYS

- 1 + **€38,75**

ADD TO CART

Qty 1-10
€38,75
Qty 11+
€38,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40

Cut-Off Position λ_c (nm):
300±6

Cut-On Wavelength (nm): 300.00
Density (g/cm³): 2.51
Glass/Filter Number: SCHOTT N-WG295
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 400.00
Spectral Transmittance t_p (%): 99.00
Stopband Limit λ_s(nm): 250.00
Surface Quality: 80-50
Transformation Temperature (°C): 565.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

Reach 181: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View