

[All Products](#) / [Lab and Production](#) / [Optical Adhesives](#) / [Norland Optical Adhesives](#)

[See all 48 Products in Family](#)

Norland Optical Adhesive NOA 165H, 1 oz. Application Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA 165H, 1 oz Application Bottle

Stock **#17-362** 3-4 DAYS

⊖ 1 ⊕ **€87,00**

ADD TO CART

Qty 1-4

€87,00

Qty 5+

€82,40

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Size (oz):
1

Glass Bonding:
Excellent

Metal Bonding:
Excellent

Plastic Bonding: Excellent
Viscosity (cps): 200 - 300
Durability: Soft & Flexible
Index of Refraction n_d: 1.65 @ 589nm
Norland Number: 165H
Shelf Life: 4 months
Type: Bottle
Typical Applications: Bonding glass to glass
Note: Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.
Absorption Range (nm): 315 - 450
Bonding Type: Glass to Glass
Energy for Full Cure (J/cm²): 6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant