

Olympus LMPLFLN-BD 50X Objective

See More by [Olympus](#)



Stock #86-830 3-4 DAYS

- 1 + **€3.820,00**

ADD TO CART

Qty 1+
€3.820,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Diameter (mm):
32.00

Field of View (mm):
0.53

Focal Length FL (mm):
3.60

Model Number:

1-U2N350
Length excluding Threads (mm): 34.40
Magnification: 50X
Maximum Diameter (mm): 32
Numerical Aperture NA: 0.50
Mounting Threads: M26 x36 TPI
Transmission (%): T> 90 from 400-700nm
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 0.67
Depth of Field (µm): 1.10
Operating Humidity: 20 - 80%RH with no condensation
Working Distance (mm): 10.6
Weight (g): 85
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--