

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

Olympus LMPLFLN-BD 5X Objective

See More by [Olympus](#)



#86-827

Stock #86-827 3-4 DAYS



1



€1.509,00

ADD TO CART

Qty 1+

€1.509,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Diameter (mm):
32.00

Field of View (mm):
5.3

Focal Length FL (mm):
36.00

Model Number: 1-U2N342
Length excluding Threads (mm): 30.00
Magnification: 5X
Maximum Diameter (mm): 32
Numerical Aperture NA: 0.13
Mounting Threads: M26 x 36 TPI
Transmission (%): T> 90 from 400-700nm
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 2.58
Depth of Field (µm): 16.27
Operating Humidity: 20 - 80%RH with no condensation
Working Distance (mm): 15.0
Weight (g): 81
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--