

Olympus MXPLFLN 20X Objective

See More by [Olympus](#)



23-721: Olympus MXPLFLN 20X Objective

Stock **#23-721** 3-4 DAYS

- 1 + **€3.096,00**

ADD TO CART

Qty 1+

€3.096,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Diameter (mm):
26.00

Field of View (mm):
1.33

Focal Length FL (mm):
9.00

Model Number: MXPLFLN20X
Length excluding Threads (mm): 42.00
Magnification: 20X
Maximum Diameter (mm): 26
Numerical Aperture NA: 0.6
Mounting Threads: RMS / 20.32mm x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (μm): 0.56
Depth of Field (μm): 0.61
Working Distance (mm): 3
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45.06
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View