

Olympus MXPLFLN 50X Objective

See More by [Olympus](#)



#23-722: Olympus MXPLFLN 50X Objective

Stock **#23-722** 3-4 DAYS

-

1

+

€4.010,00

ADD TO CART

Qty 1+

€4.010,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Diameter (mm):
26.00

Field of View (mm):
0.53

Focal Length FL (mm):
3.60

Model Number: MXPLFLN50X
Length excluding Threads (mm): 42.00
Magnification: 50X
Maximum Diameter (mm): 26
Numerical Aperture NA: 0.8
Mounting Threads: RMS / 20.32mm x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 0.42
Depth of Field (µm): 0.26
Working Distance (mm): 3
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45.06
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View