

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



#56-793

Stock #56-793 In Stock



1



€132,00

ADD TO CART

Qty 1+

€132,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Type of Drive:
Rack and Pinion

Type:
Metric

Stage Size (mm):
62 x 60

Construction:

Black Anodized Aluminum
Graduation (mm): 0.1 (Vernier)
Load Capacity, Normal (kg): 5
Load Capacity, Vertical (kg): 2
Mounting Threads: (1) M6 x 1, (8) M4 x 0.7
Note: One Knob Carrier
S.H.C.S. C'bore: N/A
Travel Per Knob Rotation (mm): 18

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View

