

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Mounted Machine Vision Filters

Stock #21-422 [CONTACT US](#)



1



€170,00

ADD TO CART

Qty 1-9

€170,00

Qty 10+

€162,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
200-530, 650-1041

Clear Aperture CA (mm):
34.00

Coating:
Hard Coated

Filter Thread: M39 x 0.50
Color: Orange
Center Wavelength CWL (nm): 590.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 75.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 41.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View
