

## Orange M86 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock **#21-507** 3-4 DAYS



1



€535,00

ADD TO CART

Qty 1-9

€535,00

Qty 10+

€508,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Blocking Wavelength Range (nm):**  
200-530, 650-1046

**Clear Aperture CA (mm):**  
81.70

**Coating:**  
Hard Coated

|                                                        |
|--------------------------------------------------------|
| <b>Filter Thread:</b><br>M86 x0.75                     |
| <b>Color:</b><br>Orange                                |
| <b>Center Wavelength CWL (nm):</b><br>590.00           |
| <b>Construction:</b><br>Mounted in Black Anodized Ring |
| <b>Full Width-Half Max FWHM (nm):</b><br>75.00         |
| <b>Mount Thickness (mm):</b><br>6.1                    |
| <b>Mount Thickness Including Threads (mm):</b><br>8.3  |
| <b>Outer Diameter (mm):</b><br>89.00                   |
| <b>Substrate Thickness (mm):</b><br>1.8                |
| <b>Type:</b><br>Mounted Imaging Filter                 |
| <b>Minimum Transmission (%):</b><br>≥85                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |