

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

Pixelink M-Series M2M-CYL Microscopy Monochrome Camera



Stock #17-818 3-4 DAYS

- 1 + €1.295,00

ADD TO CART

Qty 1+

€1.295,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.0

Type:
Monochrome Microscopy Camera

Manufacturer:
Pixelink

Mounting Threads:
No Mounting Threads/Tripod Adapter

Image Buffer:
Not Specified

Camera Family: M-Series
Model Number: M2M-CYL
Imaging Sensor: CMOSIS CMV2000
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 2.20
Pixels (H x V): 2,048 x 1,088
Pixel Size, H x V (µm): 5.5 x 5.5
Sensing Area, H x V (mm): 11.3 x 6.0
Frame Rate (fps): 169.80
Pixel Depth: 8/10 bit
Exposure Time: Not Specified
Connector: USB 3.0, Micro-B
Power Supply: Power over USB
Power Consumption (W): Not Specified
GPIOs: None
Synchronization: Software Trigger
Dimensions (mm): 85.68 x 54.01 (excludes lens mount)
Weight (g): 218.5
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 60
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -45 to +85
GPIO Connector Type: None
Machine Vision Standard: USB3 Vision

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View