

Pixelink M-Series M5C-CYL Microscopy Color Camera



Stock #17-821 3-4 DAYS

- 1 + **€1.595,00**

ADD TO CART

Qty 1+
€1.595,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.0

Type:
Microscopy Camera

Manufacturer:
Pixelink

Mounting Threads:
No Mounting Threads/Tripod Adapter

Image Buffer:
Not Specified

Camera Family: M-Series
Model Number: M5C-CYL
Imaging Sensor: ON Semi Vita 5000
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1"
Resolution (MegaPixels): 5.30
Pixels (H x V): 2,592 x 2,048
Pixel Size, H x V (µm): 4.8 x 4.8
Sensing Area, H x V (mm): 12.4 x 9.8
Frame Rate (fps): 75.30
Pixel Depth: 8/10 bit
Exposure Time: Not Specified
Connector: USB 3.0, Micro-B
Power Supply: Power over USB
Power Consumption (W): Not Specified
GPIOs: None
Synchronization: Software Trigger
Dimensions (mm): 82.69 x 54.01 (excludes lens mount)
Weight (g): 218.5
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 53
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -45 to +85
GPIO Connector Type: None
Machine Vision Standard: USB3 Vision

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View