

[See all 15 Products in Family](#)

Pixelink RJ45 coupler female to female



Stock **#23-895** **2 In Stock**

- 1 + €11^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€11,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Coupler

Model Number:

PL-CC-32

Regulatory Compliance

RoHS 2015:

Compliant

Reach 224:

Compliant	
View	Certificate of Conformance:

Product Details

- 10GBASE-T (10GigE) Ethernet Interface, 10X Faster than GigE
 - 7.0 to 24.0 Megapixel Sony 4th Gen Pregius S Sensors
 - Fully Compatible with Pixelink Capture Software and SDK
- Pixelink PL-X 10GigE Cameras, utilizing the latest 10GBASE-T Gigabit Ethernet interface, are capable of providing high quality, reliable image transfers at cable lengths of up to 100m on CAT6A. These global shutter cameras offer up to 24MP Resolution with framerates up to 154FPS via the Sony Pregius 2nd, 3rd and 4th generation sensors. Additionally, these cameras feature Power over Ethernet (PoE), Trigger over Ethernet (ToE) and IEEE1588 clock synchronization (PTP), and are fully compatible with Pixelink Capture Software and SDK. Pixelink PL-X10GigE Cameras are ideal for three-dimensional mapping, analytical research, AR/VR applications, as well as automated inspection and life science imaging.
- Note:** Pixelink Capture is a free, user-friendly application included with all Pixelink cameras, offering real-time image and video capture through an intuitive graphical interface. In contrast, the Pixelink SDK is a comprehensive development toolkit for Windows and Linux that enables developers to build custom applications with full camera control via C/C++, .NET, or Python. The SDK is available as a trial download, allowing users to evaluate its capabilities before purchasing a license. Links to software downloads (SDK and Capture) are available on the product pages.