

Power Supply for 0.5-0.8mW HeNe Laser, 24 VDC, Bare Wire Leads



L28 Series with CDRH Delay HeNe Laser Power Supply

Stock #11-383 3-4 DAYS

⊖ 1 ⊕

€331,00

ADD TO CART

Qty 1+

€331,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (inches):
4.00 x 1.50 x 1.00

Type:
OEM

Output Voltage (V):
1250

Output Current (mA):
4

Compatible Laser Models:

[1108](#), [1108P](#), [1107](#), [1107P](#)

Output Power (W):
5

Input Current (A):
0.95 (Max. Current Draw)

Connector:
High Voltage Alden Connector

Input Voltage (V):
22-30 DC

Model Number:
L28 Series

Compatible Laser Stock Number:
[#62-714](#), [#62-715](#), [#62-716](#), [#62-717](#)

Features:
CDRH Delay (3-5 seconds)

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)