

Power Supply for 10mW HeNe Laser, AC, Bare Wire Leads



SL93 Series Power Supply (#11-381)

Stock **#11-381** 20+ In Stock

-

1

+

€700⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€700,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads



General

OEM

Type:

Compatible Laser Models:

1135, 1135P

SL93 Series

Model Number:

Compatible Laser Stock Number:

#62-726, #62-727

CDRH Delay (3-5 seconds)		Features:
Physical & Mechanical Properties		
7.05 x 2.30 x 1.40		Dimensions (inches):
Electrical		
20.15		Output Power (W):
0.75 (Max. Current Draw)		Input Current (A):
Hardware & Interface Connectivity		
3100		Output Voltage (V):
6.5		Output Current (mA):
High Voltage Alden Connector		Connector:
100-250, 60/50Hz		Input Voltage (V):
Regulatory Compliance		
View		Certificate of Conformance:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

