

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



L28 Series with CDRH Delay HeNe Laser Power Supply

Stock #11-384 [CONTACT US](#)



1



€331,00

ADD TO CART

Qty 1+

€331,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (inches):
4.00 x 1.50 x 1.00

Type:
OEM

Output Voltage (V):
1700

Output Current (mA):
4.9

Compatible Laser Models:

[1101](#), [1101P](#), [1103](#), [1103P](#)

Output Power (W):
8.33

Input Current (A):
3 (Max. Current Draw)

Connector:
High Voltage Alden Connector

Input Voltage (V):
10-14 DC

Model Number:
L23 Series

Compatible Laser Stock Number:
[#62-718](#), [#62-719](#), [#64-103](#), [#64-104](#)

Features:
CDRH Delay (3-5 seconds)

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)