

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



3cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock #17-391

CONTACT US



1



€26,50

ADD TO CART

Qty 1-4

€26,50

Qty 5+

€25,40

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Size (oz):  
0.1

Glass Bonding:  
Excellent

Metal Bonding:  
Good

|                                                                                                                                                                                                            |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Plastic Bonding:</b><br>Excellent/Good                                                                                                                                                                  |
| <b>Viscosity (cps):</b><br>20000 - 25000                                                                                                                                                                   |
| <b>Durability:</b><br>Hard                                                                                                                                                                                 |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.54                                                                                                                                                       |
| <b>Norland Number:</b><br>86TH                                                                                                                                                                             |
| <b>Shelf Life:</b><br>4 months                                                                                                                                                                             |
| <b>Type:</b><br>Barrel                                                                                                                                                                                     |
| <b>Typical Applications:</b><br>Applications requiring adheisve meeting Bellcore specification of 85C/85RH for bonding glass for 2000 hours                                                                |
| <b>Note:</b><br>Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure. |
| <b>Absorption Range (nm):</b><br>315 - 420                                                                                                                                                                 |
| <b>Bonding Type:</b><br>Glass to Glass/Plastic                                                                                                                                                             |
| <b>Energy for Full Cure (J/cm<sup>2</sup>):</b><br>2.5                                                                                                                                                     |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |