

[See all 22 Products in Family](#)

Red, 1" High Brightness LED Diffuse Axial Illuminator

See More by [Advanced Illumination](#)



Advanced Illumination Diffuse Axial LED Illuminators

Stock **#36-552** **1 In Stock**

-

1

+

€685^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€685,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
DL225-025625IC	Model Number:
LED Illuminator	Type of Illumination:
Advanced Illumination	Manufacturer:
Diffuse Axial	Geometry:

Illumination Mode:

Constant

Physical & Mechanical Properties

Dimensions (mm):

106 L x 33 W x 36 T

Weight (g):

187.89

Aperture Size:

~1.1"x1.1"

Optical Properties

Color:

Red

Wavelength (nm):

625

Working Distance (mm):

25

Hardware & Interface Connectivity

Connector:

Flying Leads

Power Supply:

Power Supply Required and Sold Separately.

USA: #66-855

Europe: **#66-855**

Japan: #89-513

Korea: #33-773

China: **#66-855**

Environmental & Durability Factors

Operating Temperature (°C):

0 to +60

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

View

Reach 233:

Contains SVHC(s)

Product Details

- Bright, Consistent Diffuse Illumination Over Field of View
- Unique Modular Heat Sink Design
- Internal Beamsplitter Ideal for Inspecting Highly Reflective Objects
- Excellent Light Stability

Advanced Illumination Diffuse Axial LED Illuminators are ideal for inspecting highly reflective optics. These coaxial illuminators provide even illumination over the field coverage. Advanced Illumination Diffuse Axial LED Illuminators feature vibration free performance and easily mount via M6 threaded holes.

Note: Required 24V power supply #66-855. Accessories for Advanced Illumination products are available and sold separately. Units cannot be intensity controlled.

Technical Information

