

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #66-096 3-4 DAYS



1



€88,00

ADD TO CART

Qty 1-10

€88,00

Qty 11+

€78,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00

Cut-Off Position λ_c (nm):
630±6

Cut-On Wavelength (nm): 630.00
Density (g/cm³): 2.65
Glass/Filter Number: SCHOTT RG630
Coating: Uncoated
Color: Red
Passband Limit 1 λ_{p1} (nm): 710.00
Spectral Transmittance t_p (%): 94.00
Stopband Limit λ_s(nm): 540.00
Surface Quality: 80-50
Transformation Temperature (°C): 527.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View