


SCHOTT RG-665, 25.4mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#45-070** 3-4 DAYS

- 1 + **€38,75**

ADD TO CART

Qty 1-10
€38,75

Qty 11+
€38,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40

Cut-Off Position λ_c (nm):
665±6

Cut-On Wavelength (nm): 665.00
Density (g/cm³): 2.77
Glass/Filter Number: SCHOTT RG665
Coating: Uncoated
Color: Red
Passband Limit 1 λ_{p1} (nm): 750.00
Spectral Transmittance t_p (%): 96.00
Stopband Limit λ_s(nm): 580.00
Surface Quality: 80-50
Transformation Temperature (°C): 527.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d: 0.91
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View