

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

RGB Adjustable LED Ring Light



Stock #34-864 3-4 DAYS

1 €840,00

ADD TO CART

Qty 1+

€840,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
RGB

Connector:
M12, 5 pins

Inner Diameter (mm):
58.0

Input Voltage (V):
24V DC

Mount: M4 (x4) and 3.5mm Thru (x4)
Operating Temperature (°C): -10 to 50
Dimensions (mm): 151.0 x 117.0 x 40.0
Weight (g): 400
Power Supply: Power Supply Required and Sold Separately. USA: #15-874 Europe: #15-875 Japan: #15-874 Korea: #15-874 China: #15-874
Type of Illumination: LED Illuminator
Note: Power Supply #34-871 (110V) or #34-872 (220V) (sold separately) will not provide individual color control.
Geometry: Ring Light
Illumination Mode: Strobed or Constant
Environmental Rating: IP65

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View