

[See all 12 Products in Family](#)

Blue, Ethernet High Intensity Coaxial Spot Light

See More by [Advanced Illumination](#)



Stock **#21-358** **3 In Stock**

-

1

+

€565^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€565,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
SL162-455C1	Model Number:
50,000	LED Lifetime (hours):
1	Number of LEDs:
	Type of Illumination:

LED Illuminator	
Required Controller #18-645 ; Required Power Supply #66-855	Note:
Advanced Illumination	Manufacturer:
Spot Light	Geometry:
Constant, Pulsed, Gated	Illumination Mode:

Physical & Mechanical Properties

85.1	Weight (g):

Optical Properties

Blue	Color:
455	Wavelength (nm):

Hardware & Interface Connectivity

C1	Connector:
Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	Power Supply:

2	Length of Cable (m):

Environmental & Durability Factors

0 to +60	Operating Temperature (°C):

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Controllable via Ethernet GUI or Web Browser
 - Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
 - Efficient Thermal Management for Long LED Life
 - Compatible with [TECHSPEC® Telecentric Backlight Illuminators](#) and [Lenses](#)
- Advanced Illumination Ethernet Controlled High Intensity In-Line Lights utilize a C1 connector to connect to the DCS-100E Single Output Controller (#18-645). The DCS-100E Single Output Controller allows these high intensity in-line lights to be ethernet controlled through a downloadable software package or through a Web Based Graphical User Interface (GUI). With efficient thermal management, these in-line lights are able to provide 33,000 Lux at a working distance of 100mm with a spot size of 61mm in either a continuous, pulsed, or gated operating mode. Advanced Illumination Ethernet Controlled High Intensity In-Line Lights can be overdriven in short pulses without damaging the LED through Advanced Illumination's SignaTech™ Control System which is available with the DCS-100E Controller. These lights are available in UV, Blue, Green, Red Orange, IR, or White and are compatible with the 8mm port found on many in-line illumination imaging lenses, making them an excellent choice for use with TECHSPEC® Telecentric Backlight Illuminators and telecentric lenses with an [inline illumination port](#). For applications that do not require ethernet controlled functionality, [Advanced Illumination High Intensity In-Line Lights](#) are also available.
- Note:** 24V power supply ([#66-855](#)) and DCS-100E Single Output Controller ([#18-645](#)) are required for use.