

TECHSPEC[®] Rugged Blue Series Kit, M12 Mount



C Series: All lenses pictured may not be included in the kit. See "Contents of Kit" specification for included lenses.



Stock **#73-074** [CONTACT US](#)

-

1

+

€1.764⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.764,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Rugged Blue Series	Series:
C-Mount to M12 Adapter w/O-Ring, M12 Lens Holder for Camera Boards, and 10 pack of M12 Lock Nuts Included	Note:

Contents of Kit:

36-343
36-344
36-346
36-352
36-353
36-355
37-382
37-383
37-385
36-368
36-369
36-371
36-376
36-377
36-379
36-384
36-385
36-387
59-241
66-382
16-788

Included Focal Lengths or Magnifications:

2, 4, 6, 10, 16, 25

Optical Properties

Included F#:

2.5, 4, 8

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Easy to Order Kits of Our Best Selling Fixed Focal Length Imaging Lenses
- Full Product Line or Select Focal Lengths Kit Versions Available
- TECHSPEC [C](#), [UC](#), and [HP](#) Imaging Lenses are Also Sold Individually

TECHSPEC® Imaging Lens Kits provide sets of TECHSPEC C, UC, and HP Imaging Lenses in easy to order kits at a reduced price. These kits offer multiple solutions to applications requiring fixed focal lengths such as factory automation, machine vision, inspection, or rapid prototyping. TECHSPEC Imaging Lens Kits can be ordered as a full product line or as curated selections of focal lengths within the product line. The TECHSPEC C, UC and HP lenses in these kits are C-Mount camera compatible, and feature a locking iris and focus adjustment to prevent unwanted adjustments.

- [C Series](#): Compact (C), FA Lenses for Machine Vision
- [UC Series](#): Ultra-Compact (UC), High Resolution Lenses for Small Sensors
- [HP Series](#): High Performance (HP), C-Mount Lenses for Machine Vision