


SCHOTT AS87ECO, 30mm Dia., 0.1mm Thick, Ultra-Thin Window

See More by [SCHOTT Optical Components](#)



Stock #20-213 3-4 DAYS

⊖ 1 ⊕ **€35,00**

ADD TO CART

Qty 1-10
€35,00

Qty 11+
€28,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Abbe Number (v_d):
59.5

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm): 27.00
Diameter (mm): 30.00 ±0.127
Thickness (mm): 0.10 ±0.01
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 8.7
Density (g/cm³): 2.46
Index of Refraction n_d: 1.504
Knoop Hardness (kg/mm²): 500
Poisson's Ratio: 0.216
Substrate: AS 87 ECO
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 200 - 3200
Young's Modulus (GPa): 73.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant