

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

SCHOTT BG60, 129 X 97mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT BG Glass (glass color will vary by product specification)

Stock #16-904 3-4 DAYS



1



€349,00

ADD TO CART

Qty 1-10

€349,00

Qty 11+

€304,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
129.0 x 97.0 +3.0/-0.0

Density (g/cm³):
2.83

Glass/Filter Number:
[SCHOTT BG60](#)

Length (mm): 129.00
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.53
Transformation Temperature (°C): 411
Thickness (mm): 4.50 ±0.5
Type: IR Cut-Off Filter
Wavelength: UV-VIS
Width (mm): 97.00
Edges: Break Edges
Reflection Factor P_d: 0.91

Regulatory Compliance

Certificate of Conformance: View
--