

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #19-336 3-4 DAYS



1



€80,00

ADD TO CART

Qty 1-10

€80,00

Qty 11+

€70,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
50.00

Density (g/cm³):  
2.53

Glass/Filter Number:

Substrate: □  
Heat Absorbing Glass

Operating Temperature (°C):  
300 Maximum

Coating:  
Uncoated

Index of Refraction n<sub>d</sub>:  
1.52

Surface Quality:  
60-40

Transformation Temperature (°C):  
599

Thickness (mm):  
2.00 ±0.2

Type:  
IR Cut-Off Filter

Dimensional Tolerance (mm):  
±0.2

Reflection Factor P<sub>d</sub>:  
0.92

Wavelength Range (nm):  
300 - 2700

Bevel:  
Protective as needed

Regulatory Compliance

Certificate of Conformance:  
[View](#)