

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #19-324 3-4 DAYS



1



€48,00

ADD TO CART

Qty 1-10

€48,00

Qty 11+

€42,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Density (g/cm³):
2.52

Glass/Filter Number:

SCHOTT KG3

Substrate: ☐
Heat Absorbing Glass

Operating Temperature (°C):
300 Maximum

Coating:
Uncoated

Index of Refraction n_d :
1.51

Surface Quality:
60-40

Transformation Temperature (°C):
581

Thickness (mm):
1.00 ±0.1

Type:
IR Cut-Off Filter

Dimensional Tolerance (mm):
±0.2

Reflection Factor P_d :
0.92

Wavelength Range (nm):
300 - 2700

Bevel:
Protective as needed

Regulatory Compliance

Certificate of Conformance:
[View](#)