

SCHOTT N-WG280, 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-403** 3-4 DAYS

- 1 + **€32,00**

ADD TO CART

Qty 1-10
€32,00
Qty 11+
€28,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
280.00 ±6

Density (g/cm³): 2.51
Glass/Filter Number: SCHOTT N-WG280
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 380
Index of Refraction n_d : 1.52
Spectral Transmittance t_p (%): 99
Stopband Limit λ_s (nm): 230
Surface Quality: 60-40
Transformation Temperature (°C): 558
Thickness (mm): 1.00 ±0.1
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
