

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



SCHOTT NG Glass (glass color will vary by product specification)

Stock #16-925 3-4 DAYS



1



€338,00

ADD TO CART

Qty 1-10

€338,00

Qty 11+

€305,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
165.0 x 165.0 +3.0/-0.0

Density (g/cm³):
2.41

Glass/Filter Number:
[SCHOTT NG11](#)

Length (mm): 165.00
Coating: Uncoated
Color: Gray
Index of Refraction n_d: 1.50
Transformation Temperature (°C): 481
Thickness (mm): 4.50 ±0.5
Type: Neutral Density Filter
Wavelength: VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Certificate of Conformance: View
--