

SCHOTT OG570, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT OG Glass (glass color will vary by product specification)



Stock **#16-929** 3-4 DAYS

-

1

+

€263,00

ADD TO CART

Qty 1-10
€263,00
Qty 11+
€236,00
Volume Pricing
Request Quote
ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads
Dimensions (mm): 165.0 x 165.0 +3.0/-0.0
Density (g/cm³): 2.56

Glass/Filter Number: SCHOTT OG570
Length (mm): 165.00
Coating: Uncoated
Color: Orange
Index of Refraction n_d: 1.51
Transformation Temperature (°C): 510
Thickness (mm): 4.50 ±0.5
Type: Longpass Filter
Wavelength: VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Certificate of Conformance: View
