


# SCHOTT RG1000, 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-429** ☐ In Stock

-

1

+

**€32,00**

ADD TO CART

|          |
|----------|
| Qty 1-10 |
| €32,00   |

|         |
|---------|
| Qty 11+ |
| €28,00  |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

## Get Product Downloads

**Diameter (mm):**  
12.50

**Cut-On Wavelength (nm):**  
1,000.00 ±6

|                                                       |
|-------------------------------------------------------|
| Density (g/cm³):<br>2.73                              |
| Glass/Filter Number:<br><a href="#">SCHOTT RG1000</a> |
| Coating:<br>Uncoated                                  |
| Color:<br>Black                                       |
| Passband Limit 1 $\lambda_{p1}$ (nm):<br>1300         |
| Index of Refraction $n_d$ :<br>1.54                   |
| Spectral Transmittance $t_p$ (%):<br>90               |
| Stopband Limit $\lambda_s$ (nm):<br>730               |
| Surface Quality:<br>60-40                             |
| Transformation Temperature (°C):<br>476               |
| Thickness (mm):<br>1.00 ±0.1                          |
| Type:<br>Longpass Filter                              |
| Wavelength:<br>IR                                     |
| Dimensional Tolerance (mm):<br>±0.2                   |
| Reflection Factor $P_d$ :<br>0.91                     |
| Bevel:<br>Protective as needed                        |

## Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| Certificate of Conformance:<br><a href="#">View</a> |
|-----------------------------------------------------|