

SCHOTT RG645, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT RG Glass (glass color will vary by product specification)



Stock **#16-934** 3-4 DAYS



1



€263,00

ADD TO CART

Qty 1-10

€263,00

Qty 11+

€236,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
165.0 x 165.0 +3.0/-0.0

Density (g/cm³):
2.65

Glass/Filter Number: SCHOTT RG645
Length (mm): 165.00
Coating: Uncoated
Color: Red
Index of Refraction n_d: 1.52
Transformation Temperature (°C): 519
Thickness (mm): 4.50 ±0.5
Type: Longpass Filter
Wavelength: VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Certificate of Conformance: View
