


SCHOTT RG665, 50mm Sq., 2mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-521** ☐ In Stock



1



€77,50

ADD TO CART

Qty 1-10
€77,50
Qty 11+
€76,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Cut-On Wavelength (nm):
665.00 ±6

Density (g/cm³): 2.77
Glass/Filter Number: SCHOTT RG665
Length (mm): 50.00
Coating: Uncoated
Color: Red
Passband Limit 1 λ_{p1} (nm): 750
Index of Refraction n_d : 1.54
Spectral Transmittance t_p (%): 96
Stopband Limit λ_s (nm): 580
Surface Quality: 60-40
Transformation Temperature (°C): 527
Thickness (mm): 2.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.91
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View