

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #16-457 3-4 DAYS



1



€32,00

ADD TO CART

Qty 1-10

€32,00

Qty 11+

€28,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
726.00

Density (g/cm³): 2.58
Glass/Filter Number: SCHOTT RG9
Coating: Uncoated
Color: Black
Index of Refraction n_d: 1.52
Surface Quality: 60-40
Transformation Temperature (°C): 519
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: IR
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--