

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



SCHOTT RG9 Glass (glass color will vary by product specification)

Stock #16-931 3-4 DAYS



1



€263,00

ADD TO CART

Qty 1-10

€263,00

Qty 11+

€236,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):  
165.0 x 165.0 +3.0/-0.0

Density (g/cm³):  
2.58

Glass/Filter Number:  
[SCHOTT RG9](#)

|                                                      |
|------------------------------------------------------|
| <b>Length (mm):</b><br>165.00                        |
| <b>Coating:</b><br>Uncoated                          |
| <b>Color:</b><br>Black                               |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.52 |
| <b>Transformation Temperature (°C):</b><br>519       |
| <b>Thickness (mm):</b><br>4.50 ±0.5                  |
| <b>Type:</b><br>Longpass Filter                      |
| <b>Wavelength:</b><br>IR                             |
| <b>Width (mm):</b><br>165.00                         |
| <b>Edges:</b><br>Break Edges                         |
| <b>Reflection Factor <math>P_d</math>:</b><br>0.92   |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
|------------------------------------------------------------|