

SCHOTT UG11, 12.5mm Dia., 2mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-372** 3-4 DAYS

[Additional Bandwidths](#)

- 1 + **€47,00**

ADD TO CART

Qty 1-10
€47,00
Qty 11+
€41,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
325.00

Density (g/cm³): 2.92
Glass/Filter Number: SCHOTT UG11
Coating: Uncoated
Color: Black
Index of Refraction n_d: 1.56
Surface Quality: 60-40
Transformation Temperature (°C): 545
Thickness (mm): 2.00 ±0.2
Type: Bandpass Filter
Wavelength: UV
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--