

Sealed 300mm 635nm Line Light



Stock #74-187 NEW **1 In Stock**

€2.365⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€2.365,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Collimated **Type of Optics:**

LED Illuminator **Type of Illumination:**

Compatible with #18-645 external controller **Note:**

Advanced Illumination **Manufacturer:**

Geometry:

Line Light

Illumination Mode:

Constant

Physical & Mechanical Properties

Length (mm):

300.00

Dimensions (mm):

309.9 L x 51.1 W

Weight (g):

1442

Optical Properties

Color:

Red

Wavelength (nm):

635

Working Distance (inches):

0.5-23

Hardware & Interface Connectivity

Connector:

4-pin Male M12

Operating Voltage (V):

24V DC, 3A

Power Supply:

Power Supply Required and Sold Separately: [#73-977](#)

Threading & Mounting

Mount:

T-Slot for M6 Nut

Environmental & Durability Factors

Operating Temperature (°C):

0 °C to 35 °C

Environmental Rating:

IP67

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Contains SVHC\(s\)](#)

Product Details

- IP67 For Dust and Debris Protection
- High Intensity Illumination Profile
- Available in UV, White, Blue, Green, Red, & NIR
- Ideal For Line Scan Applications

The Advanced Illumination Sealed High Intensity Line Lights provide a uniform illumination profile for line scan applications in rugged environments. These lights are IP67-rated for protection against dust, debris, and liquid, offering reliable performance in harsh environments. The lights are available in UV, white, blue, green, red, and NIR wavelengths and are passively cooled for continuous long-term operation. The Advanced Illumination High Intensity Line Lights feature an embedded controller that is designed for continuous operation and housed within the light itself. These lights are ideal for rugged line scan applications including inspection of sheetrock, lumber, and ceramics, and food and beverage washdown environments.