

Sectional LED Ring Light, 220V



Stock #68-770 **1 In Stock**

⊖ 1 ⊕ €260⁰⁰

ADD TO CART

Volume Pricing

Qty 1-5	€260,00 each
Qty 6+	€234,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

72.00 **Number of LEDs:**

LED Illuminator **Type of Illumination:**

Note:
Power Supply Included
Requires 110V to 220V Inversion for Use in the US

Ring Light **Geometry:**

Constant

Illumination Mode:

Physical & Mechanical Properties

60.5

Inner Diameter (mm):

Optical Properties

White

Color:

Hardware & Interface Connectivity

220.00

Operating Voltage (V):

Environmental & Durability Factors

6400.00

Color Temperature (K):

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Large Inner Diameters for Easy Mounting
- 6400K Color Temperature
- Features Sectional Light Control

LED Ring Light Illuminators are strong alternatives to traditional fluorescent ring lights. The sectional ring light features lighting control in each of the unit's four quadrants, a 60.5mm inner diameter, and 72 LEDs. The sectional ring light is controlled using a panel on the top of the unit. LED Ring Light Illuminators are ideal for use with reflective parts and features a 70mm inner diameter and 60 LED bulbs. Sectional Light Control and Polarizer/Analyzer models are available.

Note: Due to CE restrictions, [#68-771](#) Polarizer/Analyzer LED Ring Light is not available in all regions. Please [contact us](#) for a suitable replacement.
