

[See all 10 Products in Family](#)

## SMO 10° Single Element Lens Reel



Stock #90-765 **NEW** 3 In Stock

- 1 + €750<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€750,00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

This is a reel of 350 optics

#### Contents of Kit:

Clamp-ring soldered

#### Note:

### Physical & Mechanical Properties

10.50

Diameter (mm):

8.74mm **Height (mm):**

## Optical Properties

**Substrate:**   
SILASTIC™ MS-1002 Moldable Silicone

**Color:**  
White

**Overall Efficiency (%):**  
0.84

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- Five Lens Shape Options
- Over 90% Efficient from UV-A through Visible and Near IR
- Solder Pads Allow for High-Precision Placement

LumenFlow Surface Mount Optics deliver high optical efficiency in a compact, low-profile package that easily integrates into photonic assemblies. Molded with tight tolerances, each optic ensures repeatable performance across production batches. Designed for automated placement and soldering on a PCB simultaneously with SMT components, these optics support high-volume manufacturing workflows while reducing assembly costs and cycle times. LumenFlow Surface-Mount Optics are made with optical grade silicone which doesn't melt or reflow and has an operating temperature of 200C. Silicone is also water resistant, submersible, UV resistant, and resists impact and environmental wear, ensuring long-term stability in demanding applications. Available in a broad range of focal lengths, and form factors, these optics meet the needs of diverse machine-vision, sensing and illumination applications from UV-A to 1.6µm.

## Technical Information

- 
- 
- 
- 
-