

Universal Right Angle Bracket, Pair



Universal Right Angle Bracket (#11-157)

Stock #11-158 **15 In Stock**

⊖ 1 ⊕ €262.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€262,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Note:
Downloadable documents reflect a single right angle bracket (#11-157), not a pair.

Physical & Mechanical Properties

Length (inches):
12.0

Width (inches):
6.0

Thickness (inches):
1.0

Construction:
Black Anodized Aluminum

Threading & Mounting

Mounting Threads:
(9) 1/4-20 (M6x1.0) S.H.C.S. Thru-Slots

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)

Product Details

- Universal Design Works With Metric and English Bench Plates and Breadboards
- Uses Standard 1/4-20 or M6 Socket Head Cap Screws
- Black Anodized Aluminum Construction

Universal Right Angle Brackets allow our English and Metric Economical Bench Plates to be mounted orthogonally to a Composite Breadboard or another bench plate. These brackets are made from 1" thick black anodized aluminum. Thru-slots on the vertical and horizontal arms of the bracket allow for the use of both M6 and 1/4-20 SHCS for mounting, and accommodate breadboard hole spacing of 1" and 25mm. Universal Right Angle Brackets feature a ubiquitous design that enables easy integration of additional components into any benchtop system. For applications that require more structural support, purchase the Universal Right Angle Bracket, Pair ([#11-158](#)).

Note: Not recommended for use with plates taller than 12" or 300mm.

Technical Information

