

Universal Right Angle Bracket, Pair



Universal Right Angle Bracket (#11-157)

Stock **#11-158** 20+ In Stock

-

1

+

€262⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€262,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Note:
Downloadable documents reflect a single right angle bracket (#11-157), not a pair.

Physical & Mechanical Properties

1.0	Thickness (inches):
6.0	Width (inches):
Black Anodized Aluminum	Construction:
12.0	Length (inches):

Threading & Mounting

(9) 1/4-20 (M6x1.0) S.H.C.S. Thru-Slots	Mounting Threads:
---	-------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

PRODUCT DETAILS

- Universal Design Works With Metric and English Bench Plates and Breadboards
 - Uses Standard 1/4-20 or M6 Socket Head Cap Screws
 - Black Anodized Aluminum Construction
- Universal Right Angle Brackets allow our English and Metric Economical Bench Plates to be mounted orthogonally to a Composite Breadboard or another bench plate. These brackets are made from 1" thick black anodized aluminum. Thru-slots on the vertical and horizontal arms of the bracket allow for the use of both M6 and 1/4-20 SHCS for mounting, and accommodate breadboard hole spacing of 1" and 25mm. Universal Right Angle Brackets feature a ubiquitous design that enables easy integration of additional components into any benchtop system. For applications that require more structural support, purchase the Universal Right Angle Bracket, Pair (#11-158).

Note: Not recommended for use with plates taller than 12" or 300mm.

TECHNICAL INFORMATION

