

Vis M39 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-421 3-4 DAYS



1



€153,00

ADD TO CART

Qty 1-9

€153,00

Qty 10+

€145,80

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
351 -380, 720-1100

Clear Aperture CA (mm):
34.00

Coating:
Hard Coated

Filter Thread: M39 x 0.50
Color: Vis
Center Wavelength CWL (nm): 550.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 300.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 41.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View