

Vis M86 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-506 3-4 DAYS



1



€481,00

ADD TO CART

Qty 1-9

€481,00

Qty 10+

€457,40

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
356 -380, 720-1100

Clear Aperture CA (mm):
81.70

Coating:
Hard Coated

Filter Thread: M86 x0.75
Color: Vis
Center Wavelength CWL (nm): 550.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 300.00
Mount Thickness (mm): 6.1
Mount Thickness Including Threads (mm): 8.3
Outer Diameter (mm): 89.00
Substrate Thickness (mm): 1.8
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
