

White Adjustable LED Ring Light



Stock #34-861 3-4 DAYS

⊖ 1 ⊕ **€690,00**

ADD TO CART

Qty 1+

€690,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
White

Connector:
M12, 5 pins

Inner Diameter (mm):
58.0

Input Voltage (V):
24V DC

Mount: M4 (x4) and 3.5mm Thru (x4)
Operating Temperature (°C): -10 to 50
Dimensions (mm): 151.0 x 117.0 x 40.0
Weight (g): 400.00
Power Supply: Power Supply Required and Sold Separately. USA: #15-874 Europe: #15-875 Japan: #15-874 Korea: #15-874 China: #15-874
Type of Illumination: LED Illuminator
Geometry: Ring Light
Illumination Mode: Strobed or Constant
Environmental Rating: IP65

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View