

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #63-334 CLEARANCE 3-4 DAYS



1



€299,95

ADD TO CART

Qty 1+

€299,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
White

Full Width-Half Max FWHM (nm):
30.00

Height (mm):
11.00

Length (mm):
98.00

Mounting Threads: M3
Width (mm): 25.00
LED Lifetime (hours): 100,000
Power Supply: Power Supply Required and Sold Separately. USA: #59-433 Europe: Not Available Japan: #59-433 Korea: Not Available China: #59-433
Spot Size at 100mm Working Distance (mm): 10.00
Irradiance at 100mm (W/m²): N/A
Type of Illumination: LED Illuminator
Geometry: Line Light
Illumination Mode: Strobed or Constant

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
