

YVO4 Rochon Polarizer



Stock **#68-826** CLEARANCE 3-4 DAYS

- 1 + **€649,95**

ADD TO CART

Qty 1+
€649,95

Volume Pricing
Request Quote

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
10.0

Diameter (mm):
25.40

Extinction Ratio:
200,000:1

Substrate: ☐
YVO4

Length (mm):
16.00

Surface Quality: 20-10
Type: Linear Polarizer
Dimensional Tolerance (mm): +0.0/-0.2
Construction: Crystalline Rochon Polarizer
Transmitted Wavefront, P-V: λ/4 @ 632.8nm
Length Tolerance (mm): ±0.1
Beam Deviation (arcmin): <3
Housing: Black Anodized Aluminum
Wavelength Range (nm): 400 - 4000
Damage Threshold, By Design: ☐ 10 J/cm² @ 1064nm, 20ns
Separation Angle (°): 9.8 - 13.0 (10 @ 1550nm)

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View