

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #64-506 3-4 DAYS

1 €209,00

ADD TO CART

Qty 1-9

€209,00

Qty 10+

€184,90

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):

75.0
Outer Diameter (mm): 102.0
Construction: Black Anodized Aluminum, Black Spring Steel Leaves, Stainless Steel Pins
Lever Diameter (mm): 3.00
Lever Length (mm): 14.50
Number of Leaves: Two Sets of 10
Spacing of Leaf Layers (mm): 3.5
Thickness (mm): 9.10

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)